



# Industrial Control Transformer

## .750KVA 208-600 - 85-130 F1

By Acme Electric  
Catalog # [CE750N007CF1](#)



ICT .750KVA 208-600 - 85-130 F1

### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Color	Black
Secondary Voltage	85-130 V
UPC	047503015018

### Dimensions

Dimensions	6.21 in x 6.38 in x 6.9 in
Height	6.9 in
Length	6.21 in
Weight	29.8 lb
Width	6.38 in

### Electrical Ratings

Primary Voltage	208/600 V
-----------------	-----------

### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• cUL Listed</li></ul>
------------------	--

### Logistics

Carton Quantity	1
Pallet Quantity	48

### Product Assets

[Catalogs - Acme Electric Catalog - Section 5 - Industrial Control Transformers](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-CE750N007CF1-SPEC-EN | REV 1/2024