



# Industrial Control Transformer

## 2KVA 240,347,380 - 120X240 F2

By Acme Electric  
Catalog # [CE2000N012CF2](#)

ICT 2KVA 240,347,380 - 120X240 F2



### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### General

Application Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Color Black  
Secondary Voltage 120 X 240 V  
UPC 047503015957

### Dimensions

Dimensions	7.98 in x 7 in x 6.9 in
Height	6.9 in
Length	7.98 in
Weight	38 lb
Width	7 in

### Electrical Ratings

Primary Voltage	240, 347, 380 V
-----------------	-----------------

### Certifications And Compliance

Certified Listed	UL Listed cUL Listed
------------------	-------------------------

### Logistics

Carton Quantity	1
Pallet Quantity	24

### Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
ACME-CE2000N012CF2-SPEC-EN | REV 6/2024