



Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 15kVA

By Acme Electric
Catalog # [GP1215000S](#)



Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 15kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	GP1215000S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	277/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208/277 V
UL Insulation Class	180°C
UPC	047503089521
Winding Material	AL
kVA	15

Dimensions

Dimensions	11.59 in x 14.12 in x 16.94 in
Height	16.94 in
Length	11.59 in
Weight	161 lb
Width	14.12 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277/480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	4

Product Assets

- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - GP1215000S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-GP1215000S-SPEC-EN | REV 6/2024