



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 5kVA

By Acme Electric
Catalog # T1005K0201CSH

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 5kVA



Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
Winding Material	CU
kVA	5

Dimensions

Dimensions	7.13 in x 10.31 in x 14.38 in
Height	14.38 in
Length	7.13 in
Weight	75 lb
Width	10.31 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications And Compliance

Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)

[SDS - HCC SDS](#)

[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-T1005K0201CSH-SPEC-EN | REV 6/2024