



Buck-Boost Transformer - Single Phase, 120 X 240 - 12/24V, 10kVA

By Acme Electric
Catalog # [T211689](#)

Buck-Boost Transformer - Single Phase, 120 X 240 - 12/24V, 10kVA



*Representative Image

Features

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 X 240 V
Product Category	Buck-Boost Transformer
Secondary Voltage	12/24 V
UL Insulation Class	180°C
UPC	047503172704
Winding Material	AL
kVA	10

Dimensions

Dimensions	11.59 in x 11.75 in x 20.81 in
Height	20.81 in
Length	11.59 in
Weight	160 lb
Width	11.75 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120 X 240 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[3D Models - Group_30](#)
[Brochures - Buck-Boost Transformers](#)
[Catalogs - Acme Electric Catalog - Section 6 - DIN-Rail Power Supplies/Receptacles and Low Voltage Lighting Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Installation Manuals - Buck & Boost Transformer Installation Instructions](#)
[Installation Manuals - Manual A-701953-A](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - Product Information Video Series - Buck Boost Transformers](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-T211689-SPEC-EN | REV 1/2024