



Buck-Boost Transformer - Single Phase, 120 X 240 - 16/32V, 10kVA

By Acme Electric
Catalog # T213079

Buck-Boost Transformer - Single Phase, 120 X 240 - 16/32V, 10kVA



*Representative Image

Features

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

General

Catalog Number	T213079
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 X 240 V
Product Category	Buck-Boost Transformer
Secondary Voltage	16/32 V
UL Insulation Class	180°C
UPC	047503177709
Winding Material	AL
kVA	10

Dimensions

Dimensions	11.59 in x 11.75 in x 20.81 in
Height	20.81 in
Length	11.59 in
Weight	160 lb
Width	11.75 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120 X 240 V

Certifications And Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	4

Product Assets

- [Brochures - Buck-Boost Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Installation Manuals - SECONDORY VLOTAGE 16/32 BUCK & BOOST TRANSFORMER INSTALLATION INSTRUCTIONS](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - Product Information Video Series - Buck Boost Transformers](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-T213079-SPEC-EN | REV 6/2024