



# Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 208Δ - 208Y/120V, 15kVA

By Acme Electric  
Catalog # T3015K0061CSH

Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 208Δ - 208Y/120V, 15kVA



\*Representative Image

## Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
Winding Material	AL
kVA	15

## Dimensions

Dimensions	9.03 in x 20.3 in x 18.86 in
Height	18.86 in
Length	9.03 in
Weight	245 lb
Width	20.3 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	208D V

## Certifications And Compliance

Nema Rating	NEMA 3R
UL Standard	UL 506

## Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)

[SDS - HCC SDS](#)

[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
ACME-T3015K0061CSH-SPEC-EN | REV 6/2024