



Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 75kVA

By Acme Electric
Catalog # T3075K0013B



Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 75kVA

Features

- Quiet operation with sound levels below NEMA standards

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3075K0013B
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503091142
Winding Material	AL
kVA	75

Dimensions

Dimensions	22.37 in x 28.15 in x 29.41 in
Height	29.41 in
Length	22.37 in
Weight	500 lb
Width	28.15 in

Electrical Ratings

Efficiency	98.60%
Frequency Rating	60 Hz
Primary Voltage	480D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

Logistics

Carton Quantity	1
Pallet Quantity	1

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - T3075K0013B](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-T3075K0013B-SPEC-EN | REV 6/2024