



# Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 75kVA

By Acme Electric  
Catalog # T3075K0013CSH

Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 75kVA



\*Representative Image

## Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## General

ANFC Taps	2
BNFC Taps	4
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	180°C
Winding Material	AL
kVA	75

## Dimensions

Dimensions	15.25 in x 34.68 in x 26.82 in
Height	26.82 in
Length	15.25 in
Weight	1126 lb
Width	34.68 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

## Certifications and Compliance

Nema Rating	NEMA 3R
UL Standard	UL 506

## Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)

[Installation Manuals - Acme Electric Manual A](#)

[SDS - HCC\\_SDS](#)

[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
ACME-T3075K0013CSH-SPEC-EN | REV 7/2023