



Non Linear Load Transformer - Three Phase, 208Δ - 208Y/120V, 150kVA, K13

By Acme Electric
Catalog # T3150K0064BK13S



Non Linear Load Transformer - Three Phase, 208Δ - 208Y/120V,
150kVA, K13

Features

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection

General

| | |
|----------------------|-----------------------------|
| ANFC Taps | 2 |
| BNFC Taps | 4 |
| Catalog Number | T3150K0064BK13S |
| Construction | Ventilated |
| Electrostatic Shield | Shielded |
| K Factor | 13 |
| Max Temperature Rise | 150 Degrees Celsius |
| Mounting Type | Floor |
| Primary Voltage | 208Δ |
| Product Category | Non Linear Load Transformer |
| Secondary Voltage | 208Y/120 V |
| Taps % Steps | 2.5% |
| UL Insulation Class | 220°C |
| UPC | 047503094563 |
| Winding Material | AL |
| kVA | 150 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 29.87 in x 32.9 in x 41.52 in |
| Height | 41.52 in |

| | |
|--------|----------|
| Length | 29.87 in |
| Weight | 1600 lb |
| Width | 32.9 in |

Electrical Ratings

| | |
|------------------|--------|
| Efficiency | 98.83% |
| Frequency Rating | 60 Hz |
| Primary Voltage | 208D V |

Certifications And Compliance

| | |
|---------------------------|--|
| Buy American Compliant | Contact Manufacturer |
| CSA Standard | C22.2 No. 47 |
| Dept of Energy Regulation | Meets or exceed U.S. DOE 10 CFR Part 431 |
| Nema Rating | NEMA 3R |
| UL Standard | UL 1561 |

Product Assets

[Brochures - Non-Linear Load Transformers](#)
[Catalogs - Acme Electric Catalog - Section 3 - Harmonic Mitigating & Load Isolation Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - T3150K0064BK13S](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)