



# Non Linear Load Transformer - Three Phase, 480Δ - 208Y/120V, 225kVA, K13

By Acme Electric  
Catalog # T3225K0013BK13S



Non Linear Load Transformer - Three Phase, 480Δ - 208Y/120V,  
225kVA, K13

## Features

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection

## General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3225K0013BK13S
Construction	Ventilated
Electrostatic Shield	Shielded
K Factor	13
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Non Linear Load Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503094532
Winding Material	AL
kVA	225

## Dimensions

Dimensions	35.5 in x 39.5 in x 45.6 in
Height	45.6 in
Length	35.5 in
Weight	1938 lb
Width	39.5 in

## Electrical Ratings

Efficiency	98.94%
Frequency Rating	60 Hz
Primary Voltage	480D V

## Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

## Product Assets

- [Brochures - Non-Linear Load Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 3 - Harmonic Mitigating & Load Isolation Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - T3225K0013BK13S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
ACME-T3225K0013BK13S-SPEC-EN | REV 6/2024