



Non Linear Load Transformer - Three Phase, 208Δ - 208Y/120V, 225kVA, K13

By Acme Electric
Catalog # [T3225K0064BK13S](#)



Non Linear Load Transformer - Three Phase, 208Δ - 208Y/120V,
225kVA, K13

Features

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3225K0064BK13S
Construction	Ventilated
Electrostatic Shield	Shielded
K Factor	13
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208Δ
Product Category	Non Linear Load Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503094440
Winding Material	AL
kVA	225

Dimensions

Dimensions	35.5 in x 39.5 in x 45.6 in
Height	45.6 in

Length	35.5 in
Weight	2165 lb
Width	39.5 in

Electrical Ratings

Efficiency	98.94%
Frequency Rating	60 Hz
Primary Voltage	208D V

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

Product Assets

[Brochures - Non-Linear Load Transformers](#)
[Catalogs - Acme Electric Catalog - Section 3 - Harmonic
Mitigating & Load Isolation Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm
Notice](#)
[Engineering Drawing - T3225K0064BK13S](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)