



Low Voltage Distribution Transformer - Three Phase, 600? - 208Y/120V, 300kVA, Shielded

By Acme Electric
Catalog # [T3300K0083BS](#)



Low Voltage Distribution Transformer - Three Phase, 600? - 208Y/120V, 300kVA, Shielded

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3300K0083BS
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	220°C
UPC	047503093580
Winding Material	AL
kVA	300

Dimensions

Dimensions	35.5 in x 39.5 in x 45.6 in
Height	45.6 in

Length	35.5 in
Weight	1550 lb
Width	39.5 in

Electrical Ratings

Efficiency	99.02%
Frequency Rating	60 Hz
Primary Voltage	600D V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[SDS - HCC SDS](#)
[Specifications - T3300K0083BS](#)
[Terms and Conditions - HCC Terms & Conditions](#)