



# Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 750kVA, Copper Windings

By Acme Electric  
Catalog # T3750K0013BC



Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 750kVA, Copper Windings

## Features

- Quiet operation with sound levels below NEMA standards

## General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3750K0013BC
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503093658
Winding Material	CU
kVA	750

## Dimensions

Dimensions	41.5 in x 54 in x 62.8 in
Height	62.8 in
Length	41.5 in
Weight	3408 lb
Width	54 in

## Electrical Ratings

Efficiency	99.23%
Frequency Rating	60 Hz
Primary Voltage	480D V

## Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

## Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
ACME-T3750K0013BC-SPEC-EN | REV 6/2024