



# Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 75kVA, Encapsulated

By Acme Electric  
Catalog # T3793143S

Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 75kVA, Encapsulated



\*Representative Image

## Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3793143S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503090237
Winding Material	AL
kVA	75

## Dimensions

Dimensions	15.25 in x 34.68 in x 26.82 in
Height	26.82 in
Length	15.25 in
Weight	1126 lb
Width	34.68 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

## Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

## Logistics

Carton Quantity	1
Pallet Quantity	5

## Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - T3793143S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
ACME-T3793143S-SPEC-EN | REV 6/2024