



Industrial Control Transformer

.350KVA 240X480 - 24 F3

By Acme Electric
Catalog # [CE350N013CF3](#)

ICT .350KVA 240X480 - 24 F3



Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

General

Catalog Number CE350N013CF3
Color Black

Secondary Voltage 24 V
UPC 047503016251

Dimensions

Dimensions 5.281 in x 4.5 in x 5.28 in
Height 5.28 in
Length 5.281 in
Weight 13.6 lb
Width 4.5 in

Electrical Ratings

Primary Voltage 240 X 480 V

Certifications And Compliance

Certified Listed

- UL Listed
- cUL Listed

Logistics

Carton Quantity 1
Pallet Quantity 72

Product Assets

[Catalogs - Acme Electric Catalog - Section 5 - Industrial Control Transformers](#)
[Specifications - CE350N013CF3](#)