




# Industrial Control Transformer .100KVA 240X480-120 F4

By Acme Electric  
Catalog # TB100N008F4



ICT .100KVA 240X480-120 F4

## Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

## General

Application	Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.
Color	Black
Secondary Voltage	120 V
UPC	047503011232
kVA	.100

## Dimensions

Dimensions	3.778 in x 3.375 in x 4.356 in
Height	4.356 in
Length	3.778 in
Weight	4.2 lb
Width	3.375 in

## Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

## Certifications And Compliance

Certified Listed	UL Listed
	cUL Listed

## Logistics

Carton Quantity	1
Pallet Quantity	120

## Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
ACME-TB100N008F4-SPEC-EN | REV 6/2024