



Industrial Control Transformer .500KVA 208,230,460 -115 F3

By Acme Electric
Catalog # CE500N005CF3

TFMR 1PH .500KVA 208,230,460 -115 F3



Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

General

Application Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Color Black
 Secondary Voltage 115 V
 UPC 047503014547

Dimensions

Dimensions	5.17 in x 5.25 in x 5.91 in
Height	5.91 in
Length	5.17 in
Weight	19.2 lb
Width	5.25 in

Electrical Ratings

Primary Voltage	208/230/460 V
-----------------	---------------

Certifications And Compliance

Certified Listed	UL Listed
	cUL Listed

Logistics

Carton Quantity	1
Pallet Quantity	48

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-CE500N005CF3-SPEC-EN | REV 6/2024