



Drive Isolation Transformer - Three Phase, 230Δ - 230Y/133V, 7.5kVA

By Acme Electric
Catalog # DTFA72S

Drive Isolation Transformer - Three Phase, 230Δ - 230Y/133V, 7.5kVA



*Representative Image

Features

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

General

ANFC Taps	1
BNFC Taps	1
Catalog Number	DTFA72S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	230Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	230Y/133 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503089354
Winding Material	AL
kVA	7.5

Dimensions

Dimensions	7.37 in x 19.25 in x 15.21 in
Height	15.21 in
Length	7.37 in
Weight	180 lb
Width	19.25 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	230D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	4

Product Assets

- [Brochures - Drive Isolation Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 4 - Drive Isolation and AC Line Reactors](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - Acme_DTFA72S_TECHNICAL_DRAWINGS](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-DTFA72S-SPEC-EN | REV 6/2024