



## Drive Isolation Transformer - Three Phase, 460Δ - 230Y/133V, 7.5kVA

By Acme Electric  
Catalog # [DTGA72S](#)

Drive Isolation Transformer - Three Phase, 460Δ - 230Y/133V, 7.5kVA



\*Representative Image

### Features

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

### General

ANFC Taps	1
BNFC Taps	1
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	460Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	230Y/133 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503087206
Winding Material	AL
kVA	7.5

### Dimensions

Dimensions	7.37 in x 19.25 in x 15.21 in
Height	15.21 in
Length	7.37 in
Weight	180 lb
Width	19.25 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	460D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

### Product Assets

[3D Models - Group\\_21](#)  
[Brochures - Drive Isolation Transformers](#)  
[Catalogs - Acme Electric Catalog - Section 4 - Drive Isolation and AC Line Reactors](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Engineering Drawing - Acme\\_DTGA72S\\_TECHNICAL\\_DRAWINGS](#)  
[Installation Manuals - Acme Electric Manual A](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
ACME-DTGA72S-SPEC-EN | REV 7/2023