



# Industrial Control Transformer

## 3KVA 208-600 - 85-130 F3

By Acme Electric  
Catalog # TB3000N007F3

ICT 3KVA 208-600 - 85-130 F3

### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's CE Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Catalog Number TB3000N007F3  
Color Black



Secondary Voltage 85-130 V  
UPC 047503017890

### Dimensions

Dimensions 9.06 in x 9 in x 8.87 in  
Height 8.87 in  
Length 9.06 in  
Weight 89 lb  
Width 9 in

### Electrical Ratings

Frequency Rating 50/60 Hz  
Primary Voltage 208/600 V

### Certifications And Compliance

Certified Listed

- UL Listed
- cUL Listed

### Logistics

Carton Quantity 1  
Pallet Quantity 18

### Product Assets

[Specifications - TB3000N007F3](#)