



## Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 7.5kVA

By Acme Electric  
Catalog # T243570

Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 7.5kVA



\*Representative Image

### Features

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Buck-Boost Transformer
Secondary Voltage	24/48 V
UL Insulation Class	180°C
UPC	047503182505
Winding Material	AL
kVA	7.5

### Dimensions

Dimensions	10.84 in x 11.12 in x 20.81 in
Height	20.81 in
Length	10.84 in
Weight	135 lb
Width	11.12 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

### Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

[Brochures - Buck-Boost Transformers](#)  
[Catalogs - Acme Electric Catalog - Section 7 - Buck Boost Transformers](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Installation Manuals - A-36715-1](#)  
[Installation Manuals - Manual A-701953-A](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)  
[Video - Product Information Video Series - Buck Boost Transformers](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-T243570-SPEC-EN | REV 1/2024