



Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 7.5kVA

By Acme Electric
Catalog # [T2536151S](#)

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 7.5kVA



Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503084502
Winding Material	AL
kVA	7.5

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	115 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - Group_24](#)
- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Brochures - International Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Customer Use Drawings - a-125863](#)
- [Customer Use Drawings - a-125861](#)
- [Engineering Drawing - T2536151S](#)
- [Installation Manuals - Manual A-701953-A](#)
- [SDS - HCC_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-T2536151S-SPEC-EN | REV 1/2024