



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 6kVA

By Acme Electric
Catalog # T3006K001ICSH

Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 6kVA



*Representative Image

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

| | |
|----------------------|---------------------|
| BNFC Taps | 2 |
| Construction | Encapsulated |
| Electrostatic Shield | Shielded |
| Max Temperature Rise | 115 Degrees Celsius |
| Mounting Type | Wall |
| Secondary Voltage | 208Y/120 V |
| Taps % Steps | 5.0% |
| UL Insulation Class | 180°C |
| UPC | 047503001967 |
| Winding Material | AL |
| kVA | 6 |

Dimensions

| | |
|------------|-------------------------------|
| Dimensions | 8.82 in x 14.17 in x 11.83 in |
| Height | 11.83 in |
| Length | 8.82 in |
| Weight | 140 lb |
| Width | 14.17 in |

Electrical Ratings

| | |
|------------------|--------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 480D V |

Certifications and Compliance

| | |
|-------------|---------|
| Nema Rating | NEMA 3R |
| UL Standard | UL 506 |

Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)

[Installation Manuals - Acme Electric Manual A](#)

[SDS - HCC_SDS](#)

[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME-T3006K001ICSH-SPEC-EN | REV 7/2023