



# Non Linear Load Transformer - Three Phase, 208 $\Delta$ - 208Y/120V, 75kVA, K13

By Acme Electric  
Catalog # T3075K0064BK13S



Non Linear Load Transformer - Three Phase, 208 $\Delta$  -  
208Y/120V, 75kVA, K13

## Features

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection

## General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
K Factor	13
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208 $\Delta$
Product Category	Non Linear Load Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503094204
Winding Material	AL
kVA	75

## Dimensions

Dimensions	26.88 in x 31.9 in x 35.47 in
Height	35.47 in
Length	26.88 in
Weight	500 lb
Width	31.9 in

## Electrical Ratings

Efficiency	98.60%
Frequency Rating	60 Hz
Primary Voltage	208D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

## Product Assets

[3D Models - Group\\_42](#)  
[Brochures - Non-Linear Load Transformers](#)  
[Catalogs - Acme Electric Catalog - Section 3 - Harmonic Mitigating & Load Isolation Transformers](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Engineering Drawing - T3075K0064BK13S](#)  
[Installation Manuals - Manual A-701953-A](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-T3075K0064BK13S-SPEC-EN | REV 1/2024