



Low Voltage Distribution Transformer - Three Phase, 190/200/208/220/240Δ - 400Y/231V, 15kVA

By Acme Electric
Catalog # [T379083S](#)



*Representative Image

Low Voltage Distribution Transformer - Three Phase, 190/200/208/220/240Δ - 400Y/231V, 15kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	190 / 200 / 208 / 220 / 240Δ V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	400Y/231 V
UL Insulation Class	180°C
UPC	047503166000
Winding Material	AL
kVA	15

Dimensions

Dimensions	9.03 in x 20.3 in x 18.86 in
Height	18.86 in
Length	9.03 in
Weight	300 lb
Width	20.3 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	190/200/208/220/240D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[3D Models - Group_27](#)
[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Brochures - International Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - T379083S](#)
[Installation Manuals - Acme Electric Manual A](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME-T379083S-SPEC-EN | REV 7/2023