



# Industrial Control Transformer

## .050KVA 240,480,600 - 100,120 F1

By Acme Electric  
Catalog # TB50N011F1

ICT .050KVA 240,480,600 - 100,120 F1

### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's CE Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Catalog Number TB50N011F1  
Color Black



Secondary Voltage 100, 120 V  
UPC 047503018040

### Dimensions

Dimensions 3.32 in x 3 in x 4.04 in  
Height 4.04 in  
Length 3.32 in  
Weight 2.6 lb  
Width 3 in

### Electrical Ratings

Frequency Rating 50/60 Hz  
Primary Voltage 240/480/600 V

### Certifications And Compliance

Certified Listed

- UL Listed
- cUL Listed

### Logistics

Carton Quantity 1  
Pallet Quantity 168

### Product Assets

[Specifications - TB50N011F1](#)