



Industrial Control Transformer .075KVA 240X480-120 F4

By Acme Electric
Catalog # [TB75N008F4](#)



ICT .075KVA 240X480-120 F4

Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

General

| | |
|-------------------|--------------|
| Color | Black |
| Secondary Voltage | 120 V |
| UPC | 047503011225 |
| kVA | .075 |

Dimensions

| | |
|------------|----------------------------|
| Dimensions | 3.82 in x 3 in x 4.0397 in |
| Height | 4.0397 in |
| Length | 3.82 in |
| Weight | 3.5 lb |
| Width | 3 in |

Electrical Ratings

| | |
|------------------|-------------|
| Frequency Rating | 50/60 Hz |
| Primary Voltage | 240 X 480 V |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL Listed• cUL Listed |
|------------------|--|

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 1 |
| Pallet Quantity | 168 |

Product Assets

[Catalogs - Acme Electric Catalog - Section 5 - Industrial Control Transformers](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-TB75N008F4-SPEC-EN | REV 1/2024