



Industrial Control Transformer

.075KVA 550/575/600 -110/115/120

F4

By Acme Electric
Catalog # TB75N017F4



ICT .075KVA 550/575/600 -110/115/120 F4

Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

General

Catalog Number TB75N017F4
Color Black

Secondary Voltage 110/115/120 V
UPC 047503013274
kVA .075

Dimensions

Dimensions 3.73 in x 3 in x 4.04 in
Height 4.04 in
Length 3.73 in
Weight 3.5 lb
Width 3 in

Electrical Ratings

Frequency Rating 50/60 Hz
Primary Voltage 550/575/600 V

Certifications And Compliance

Certified Listed

- UL Listed
- cUL Listed

Logistics

Carton Quantity 1
Pallet Quantity 168

Product Assets

[Specifications - TB75N017F4](#)