



# Industrial Control Transformer

## .250KVA 240X480 - 24 F4

By Acme Electric  
Catalog # [TB250N013F4](#)



ICT .250KVA 240X480 - 24 F4

### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

### General

Catalog Number           TB250N013F4  
Color                           Black

Secondary Voltage           24 V  
UPC                            047503011928  
kVA                             .250

### Dimensions

Dimensions                 4.55 in x 4.5 in x 5.29 in  
Height                       5.29 in  
Length                       4.55 in  
Weight                       10 lb  
Width                         4.5 in

### Electrical Ratings

Frequency Rating           50/60 Hz  
Primary Voltage            240 X 480 V

### Certifications And Compliance

Certified Listed           

- UL Listed
- cUL Listed

### Logistics

Carton Quantity            1  
Pallet Quantity            72

### Product Assets

[Specifications - TB250N013F4](#)