



## Medium Voltage Transformer - Three Phase, 4800Δ - 208Y//120V, 225kVA

By Acme Electric  
Catalog # [WI225K22](#)

Medium Voltage Transformer - Three Phase, 4800Δ -  
208Y//120V, 225kVA



\*Representative Image

### General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4800Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	208Y/120 V
UPC	047503098707
Winding Material	AL
kVA	225

### Dimensions

Depth	26.5 in
Height	51.5 in
Weight	1480 lb
Width	40.5 in

### Electrical Ratings

Efficiency	98.69%
Frequency Rating	60 Hz
Primary Voltage	4800D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - MediumVoltageTransformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-WI225K22-SPEC-EN | REV 1/2024