



## Medium Voltage Transformer - Three Phase, 4160Δ - 600Y//347V, 750kVA

By Acme Electric  
Catalog # [WI750K21](#)



\*Representative Image

Medium Voltage Transformer - Three Phase, 4160Δ -  
600Y//347V, 750kVA

### General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4160Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	600Y/347 V
UPC	047503099247
Winding Material	AL
kVA	750

### Dimensions

Depth	44.0 in
Height	80.0 in
Weight	4750 lb
Width	64.0 in

### Electrical Ratings

Efficiency	99.21%
Frequency Rating	60 Hz
Primary Voltage	4160D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - MediumVoltageTransformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-WI750K21-SPEC-EN | REV 1/2024