




# Industrial Control Transformer .350KVA 208-600 - 85-130 F4

By Acme Electric  
Catalog # TB350N007F4



ICT .350KVA 208-600 - 85-130 F4

### Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

### General

Application Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Color Black  
 Secondary Voltage 85/130 V  
 UPC 047503010679  
 kVA .350

### Dimensions

Dimensions	6.42 in x 5.25 in x 5.91 in
Height	5.91 in
Length	6.42 in
Weight	28.1 lb
Width	5.25 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	208/600 V

### Certifications And Compliance

Certified Listed	UL Listed cUL Listed
------------------	-------------------------

### Logistics

Carton Quantity	1
Pallet Quantity	72

### Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
ACME-TB350N007F4-SPEC-EN | REV 6/2024