



Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 0.5kVA

By Acme Electric
Catalog # [GP12500S](#)



Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 0.5kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	GP12500S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	277/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208/277 V
UL Insulation Class	155°C
UPC	047503001103
Winding Material	CU
kVA	0.5

Dimensions

Dimensions	4.2 in x 4.37 in x 9.06 in
Height	9.06 in
Length	4.2 in
Weight	19 lb
Width	4.37 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277/480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	32

Product Assets

- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - GP12500S](#)
- [SDS - HCC SDS](#)
- [Specifications - GP12500S Specification Sheet English](#)
- [Specifications - GP12500S](#)
- [Specifications - GP12500S](#)
- [Terms and Conditions - HCC Terms & Conditions](#)