



Industrial Control Transformer .075KVA 240X480 - 24 F4

By Acme Electric
Catalog # TB75N013F4

ICT .075KVA 240X480 - 24 F4



Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

General

Application Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

Color Black
 Secondary Voltage 24 V
 UPC 047503011898
 kVA .075

Dimensions

Dimensions	3.82 in x 3 in x 4.04 in
Height	4.04 in
Length	3.82 in
Weight	3.5 lb
Width	3 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

Certified Listed	UL Listed
	cUL Listed

Logistics

Carton Quantity	1
Pallet Quantity	168

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-TB75N013F4-SPEC-EN | REV 6/2024