Low Voltage Distribution Transformer - Three Phase, 208Δ - 480Y/277V, 112.5kVA

By Acme Electric
Catalog # T3112K0034B



Low Voltage Distribution Transformer - Three Phase, 208Δ - 480Y/277V, 112.5kVA

Features

- Quiet operation with sound levels below NEMA standards

Specifications

Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 1561
UL Insulation Class	220°C

Configuration

ANFC Taps	2

Current

Frequency Rating	60 Hz
Efficiency	98.74%
Primary Voltage	208D V
kVA	112.5
Primary Voltage	208Δ
Secondary Voltage	480Y/277 V

Dimensions

Length	26.88 in
Weight	750 lb.
Height	35.47 in
Width	31.9 in
Dimensions	26.88 in x 31.9 in x 35.47 in

General

Product Category	Dry Type Distribution Transformer
Taps % Steps	2.5%
Product Family	Three Phase Dry Type
Winding Material	AL
BNFC Taps	2
Product Type	Dry Type Distribution Transformer
Mounting Type	Floor
UPC	047503093290
Construction	Ventilated

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Max Temperature Rise	150 Degrees Celsius

Product Assets

Catalog [English]
Sales Drawing [English]

© 2026 Hubbell Incorporated. All rights reserved