Low Voltage Distribution Transformer - Single Phase, 190/200/208/220 X 380/400/416/440 - 120/240V, 2kVA

By Acme Electric
Catalog # TF217439S

Low Voltage Distribution Transformer - Single Phase, 190/200/208/220 X 380/400/416/440 - 120/240V, 2kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

CE Compliant	CE Marked
Catalog Number	TF217439S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 200 / 208 / 220 X 380 / 400 / 416 / 440 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503085264
Winding Material	CU
kVA	2

Dimensions

Dimensions	5.13 in x 5.5 in x 13 in
Height	13 in
Length	5.13 in
Weight	39 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/200/208/220 X 380/400/416/440 V

Certifications And Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	20

Product Assets

Brochures - General Purpose Dry-Type Distribution Transformers
Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers
Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice
Customer Use Drawings - a-700601
Customer Use Drawings - a-700602
Customer Use Drawings - a-700592
Customer Use Drawings - a-700598
Customer Use Drawings - a-700599
Customer Use Drawings - a-700600
Engineering Drawing - TF217439S
SDS - HCC SDS
Specifications - TF217439S Specification Sheet French
Specifications - TF217439S Specification Sheet English
Specifications - TF217439S
Terms and Conditions - HCC Terms & Conditions

©2025 Hubbell Incorporated. All rights reserved