



Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 167kVA

By Acme Electric
Catalog # [TP531233S](#)

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 167kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA5

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	TP531233S
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503007006
Winding Material	AL
kVA	167

Dimensions

Dimensions	35.5 in x 39.5 in x 45.6 in
Height	45.6 in



*Representative Image

Length	35.5 in
Weight	1050 lb
Width	39.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 2
UL Standard	UL 506

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - TP531233S](#)
- [SDS - HCC SDS](#)
- [Specifications - TP531233S](#)
- [Terms and Conditions - HCC Terms & Conditions](#)