



Low Voltage Distribution Transformer - Single Phase, 208 - 120/240V, 37.5kVA

By Acme Electric
Catalog # TP536491S



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 208 - 120/240V, 37.5kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA1

General

BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	220°C
UPC	047503000083
Winding Material	AL
kVA	37.5

Dimensions

Dimensions	19.37 in x 24.39 in x 25.48 in
Height	25.48 in
Length	19.37 in
Weight	257 lb
Width	24.39 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	208 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	1

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - TP536491S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-TP536491S-SPEC-EN | REV 6/2024