



Medium Voltage Transformer - Three Phase, 4160 Δ - 240 Δ V, 112.5kVA

By Acme Electric
Catalog # [WI112K17](#)



*Representative Image

Medium Voltage Transformer - Three Phase, 4160 Δ - 240 Δ V,
112.5kVA

General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4160 Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	240D V
UPC	047503098295
Winding Material	AL
kVA	112.5

Dimensions

Depth	21.8 in
Height	40.5 in
Weight	940 lb
Width	36.5 in

Electrical Ratings

Efficiency	98.52%
Frequency Rating	60 Hz
Primary Voltage	4160D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

[Brochures - MediumVoltageTransformers](#)
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-WI112K17-SPEC-EN | REV 1/2024