



* Representative image

Stud Connector, Aluminum

by ANDERSON
Catalog ID: ADSC14912

Stud Connector, Aluminum, 1-1/2-12 Stud to Cable 0.681-0.893, Straight.
STUD, AL 1-1/2-12, .681-.893 IN

Product Details

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug Holes	0
Number of Stud Threads	12
Type	Stud to Cable
UPC	096359281825

Dimensions

Angle - Stud to Conductor	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Diameter - Stud	1.5 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	1.470 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37
Conductor Diameter - Maximum	0.893 in
Conductor Diameter - Minimum	0.681 in
Conductor Diameter Range	0.681 - 0.893
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com