



Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 30kVA

By Acme Electric
Catalog # [A3030K0310B](#)

Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 30kVA



*Representative Image

Features

- Copper terminations for trouble free operation
- Lower cost solution
- 5-10 times increase in kVA

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	220/230/240
Product Category	Buck-Boost Transformer
Secondary Voltage	208 V
UL Insulation Class	180°C
UPC	047503092408
Winding Material	AL
kVA	30

Dimensions

Dimensions	7.37 in x 19.25 in x 15.21 in
Height	15.21 in
Length	7.37 in
Weight	152 lb
Width	19.25 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

- [3D Models - Group_27](#)
- [Brochures - 3PhaseBuckBoost](#)
- [Brochures - Buck-Boost Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 7 - Buck Boost Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Installation Manuals - Acme Electric Manual A](#)
- [SDS - HCC_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - Product Information Video Series - 3 Phase Buck Boost](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME_A3030K0310B_SPEC | REV 3/2023