



Drive Isolation Transformer - Three Phase, 460? - 230Y/133V, 20kVA

By Acme Electric
Catalog # [DTGA0202S](#)



Drive Isolation Transformer - Three Phase, 460? - 230Y/133V, 20kVA

Features

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

General

ANFC Taps	1
BNFC Taps	1
Catalog Number	DTGA0202S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	460Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	230Y/133 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503695241
Winding Material	AL
kVA	20

Dimensions

Dimensions	10.18 in x 20.94 in x 20.77 in
Height	20.77 in
Length	10.18 in
Weight	435 lb

Width 20.94 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	460D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	4

Product Assets

- [Brochures - Drive Isolation Transformers](#)
- [Catalogs - Drive Isolation Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - Acme_DTGA0202S_TECHNICAL_DRAWINGS](#)
- [SDS - HCC SDS](#)
- [Specifications - DTGA0202S Specification Sheet French](#)
- [Specifications - DTGA0202S Specification Sheet English](#)
- [Specifications - DTGA0202S](#)
- [Terms and Conditions - HCC Terms & Conditions](#)