



\* Representative image

## ALRB016TBC

by Acme Electric

Catalog ID: ALRB016TBC

Prop65\_Cancer&amp;Reproductive

AC Line Reactor - Three Phase, 240 Volts 6% Z - 480 Volts 3% Z - 600 Volts 2.4% Z, 1378 uH, 16 A, CE Marked

- Protects from damaging voltage drop
- Eliminates nuisance tripping
- Reduces surges and spike currents
- Longer life for motors and solid state components

### Product Details

#### General

|                      |                     |
|----------------------|---------------------|
| CE Compliant         | CE Marked           |
| Inductance           | 1378 uH             |
| Inductance Range     | 751+ uH             |
| Max Temperature Rise | 115 Degrees Celsius |
| Motor Power          | 10 HP               |
| Mounting Hole Width  | 2.00 in. (5.1 mm)   |
| Primary Voltage      | 240V / 480V / 600V  |
| Product Category     | AC Line Reactor     |
| Reactor Current      | 16 A                |
| UL Insulation Class  | 180°C               |
| UPC                  | 047503087183        |
| Winding Material     | CU                  |

#### Dimensions

|        |         |
|--------|---------|
| Height | 4.75 in |
| Length | 3.75 in |
| Weight | 6 lb    |
| Width  | 6.5 in  |

#### Electrical Ratings

|                  |               |
|------------------|---------------|
| Frequency Rating | 60 Hz         |
| Primary Voltage  | 240/480/600 V |

#### Certifications and Compliance

|              |             |
|--------------|-------------|
| CE Compliant | CE Marked   |
| CSA Standard | C22.2 No 66 |

|             |        |
|-------------|--------|
| UL Standard | UL 506 |
|-------------|--------|