



Drive Isolation Transformer - Three Phase, 575? - 460Y/266V, 220kVA

By Acme Electric
Catalog # [DTHB02204S](#)

Drive Isolation Transformer - Three Phase, 575? - 460Y/266V, 220kVA



*Representative Image

Features

- Copper terminations for trouble free operation
- Wound core and strip winding for low losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units
- Optional weather shield - WSA4

General

ANFC Taps	2
BNFC Taps	2
Catalog Number	DTHB02204S
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	575Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	460Y/266 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503090725
Winding Material	AL
kVA	220

Dimensions

Dimensions	29.88 in x 32.9 in x 41.52 in
------------	-------------------------------

Height	41.52 in
Length	29.88 in
Weight	1120 lb
Width	32.9 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	575D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561

Product Assets

- [Brochures - Drive Isolation Transformers](#)
- [Catalogs - Drive Isolation Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - Acme_DTHB02204S_TECHNICAL_DRAWINGS](#)
- [SDS - HCC SDS](#)
- [Specifications - DTHB02204S](#)
- [Specifications - DTHB02204S Specification Sheet French](#)
- [Specifications - DTHB02204S Specification Sheet English](#)
- [Terms and Conditions - HCC Terms & Conditions](#)