



* Representative image

ALRB027LWE

by Acme Electric

Catalog ID: ALRB027LWE

Prop65_Cancer&Reproductive

AC Line Reactor - Three Phase, 240 Volts 6% Z - 480 Volts 3% Z - 600 Volts 2.4% Z, 817 uH, 27 A, CE Marked, Encapsulated

- Protects from damaging voltage drop
- Eliminates nuisance tripping
- Reduces surges and spike currents
- Longer life for motors and solid state components

Product Details

General

CE Compliant	CE Marked
Construction	Encapsulated
Inductance	817 uH
Inductance Range	751+ uH
Max Temperature Rise	115 Degrees Celsius
Motor Power	20 HP
Mounting Type	Wall
Primary Voltage	240V / 480V / 600V
Product Category	AC Line Reactor
Reactor Current	27 A
UL Insulation Class	180°C
UPC	047503096468
Winding Material	CU

Dimensions

Height	11.5 in
Length	7.13 in
Weight	28 lb
Width	10.31 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240/480/600 V

Certifications and Compliance

CE Compliant	CE Marked
--------------	-----------

CSA Standard	C22.2 No 66
Nema Rating	NEMA 3R
UL Standard	UL 506