



\* Representative image

## ALRC004TBC

by Acme Electric

Catalog ID: ALRC004TBC

Prop65\_Cancer&Reproductive

AC Line Reactor - Three Phase, 240 Volts 10% Z - 480 Volts 5% Z - 600 Volts 4% Z, 9189 uH, 4 A, CE Marked

- Protects from damaging voltage drop
- Eliminates nuisance tripping
- Reduces surges and spike currents
- Longer life for motors and solid state components

### Product Details

#### General

|                      |                     |
|----------------------|---------------------|
| CE Compliant         | CE Marked           |
| Inductance           | 9189 uH             |
| Inductance Range     | 751+ uH             |
| Max Temperature Rise | 115 Degrees Celsius |
| Motor Power          | 2 HP                |
| Mounting Hole Width  | 1.44 in. (3.7 mm)   |
| Primary Voltage      | 240V / 480V / 600V  |
| Product Category     | AC Line Reactor     |
| Reactor Current      | 4 A                 |
| UL Insulation Class  | 180°C               |
| UPC                  | 004750319122        |
| Winding Material     | CU                  |

#### Dimensions

|        |          |
|--------|----------|
| Height | 3.875 in |
| Length | 3.125 in |
| Weight | 4 lb     |
| Width  | 4.25 in  |

#### Electrical Ratings

|                  |               |
|------------------|---------------|
| Frequency Rating | 60 Hz         |
| Primary Voltage  | 240/480/600 V |

#### Certifications and Compliance

|              |             |
|--------------|-------------|
| CE Compliant | CE Marked   |
| CSA Standard | C22.2 No 66 |

|             |        |
|-------------|--------|
| UL Standard | UL 506 |
|-------------|--------|