



Low Voltage Distribution Transformer - Three Phase, 480? - 208Y/120V, 45kVA, 316 Stainless Steel, Encapsulated

By Acme Electric
Catalog # [T379313SS](#)

Low Voltage Distribution Transformer - Three Phase, 480? - 208Y/120V, 45kVA, 316 Stainless Steel, Encapsulated

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T379313SS
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503130674
Winding Material	AL
kVA	45

Dimensions

Dimensions	12.76 in x 30.18 in x 25.31 in
Height	25.31 in



*Representative Image

Length	12.76 in
Weight	780 lb
Width	30.18 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - T379313SS](#)
- [SDS - HCC SDS](#)
- [Specifications - T379313SS Specification Sheet English](#)
- [Specifications - T379313SS](#)
- [Specifications - T379313SS Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)