

## Suspension Clamp

By ANDERSON  
Catalog # [2706513001](#)

The 270 series suspension clamp is a galvanized ductile iron trunnion type suspension clamp designed for use on ground wire applications with galvanized steel. The 270 series clamp is designed for use on tangent suspension spans with horizontal or vertical post insulators. Keeper is reversible for proper fit on different size ground wires. For use with conductors 0.50 - 1.06 inch diameter. Ultimate body strength is 2,800 lbs



\*Representative Image

### Features

- Anti-static spring can be supplied by adding "ARIV" to catalog number. Example, 2706513001ARIV

### General

Bolt Installation Torque (Recommended)	480 in-lbs
EU RoHS Indicator	No
Material - Clamp	Ductile Iron
Material - Hardware	Galvanized Steel
Product Category	Trunnion Clamp
Strength Rating - Ultimate Body	2800 lb
Type	Standard Voltage Suspension Clamps
UPC	096359261797
With Anti-Static Springs	No

### Dimensions

Angle - Take-Off Maximum	15 °
Bolt Diameter	0.500 in
Clamping - Maximum	1.06 in
Clamping - Minimum	0.5 in
Diameter - Insulator Attachment Holes	0.609375 in
Length	5.25 in
Weight	2.75 lb
Width	3.875 in

### Electrical Ratings

Voltage Application	Ground Wire
---------------------	-------------

### Conductor Related

Clamping Range	0.5- 1.06
----------------	-----------

### Logistics

Pallet Quantity	720
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Literature - Ropes Course Industry Letter \(April 2021\)](#)

[Sales Drawings - C-13597](#)