

Y-Clevis Eye, Rotated

By ANDERSON
Catalog # [854512000](#)

Y-clevis eyes are primarily used to attach clamping devices to yoke plates or other associated hardware in a bundle conductor assembly. The bent bolt in the Y-section provides an additional point of articulation within an assembly.



Features

- Rotated Y-Clevis Eye
- Ultimate strength is 30,000 lbs.
- Material: Body - Galvanized Forged Steel, Hardware - Galvanized Steel, Cotter Pin - Stainless Steel
- 0.688" eye hole diameter
- 0.750" bent bolt hole diameter

General

Catalog Number	854512000
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	YCS-90 Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359252443

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.688 in
Diameter - Pin	0 in
Dimensions	5.531 in x 2 in x 1.75 in
Height	1.75 in

Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	5.531 in
Length - Coupling	3.75 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.943 lb
Width	2 in
Width - Eye	0.625 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	1152
-----------------	------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - CC-13369](#)
[Specifications - 854512000](#)